


Eiki Lens Chart

LENSES FOR EK-623UW

Nov. 1, 2018

Resolution: WUXGA (1920x1200)

Aspect Ratio: (16 : 10)



Screen Dimensions.

H'	2.2	4.4	5.0	6.2	7.5	8.8	11.3	13.3
W'	3.5	7.1	8.0	10.0	12.0	14.2	18.0	21.2
D''	50	100	113	141	170	200	255	300

Factory Specifications - Standard Lens				Measurements and Calculations									
EIKI Part No.	Ref.	Diagonal	Shift Range	T/W	Throw Distance to Screen in feet.								
AH-A22030*	A02	Min: 50"	V: +/- 50%	f:2.0~2.3	1.22	4.3	8.6	9.7	12.2	14.6	17.2	21.9	25.8
		Max: 300"	H: +/- 15%		1.53	5.4	10.8	12.2	15.3	18.4	21.6	27.5	32.4

Factory Specifications - Auxiliary Lenses				Measurements and Calculations								
EIKI Part No.	Ref.	Diagonal	Shift Range	T/W	Throw Distance to Screen in feet.							
AH-A25010	A16	Min: 50"	Advanced Installation***	0.37			3.0	3.7	4.5	5.3	6.7	7.9
		Max: 300"										

AH-A22010B	A15	Min: 50"	V: +/- 50%	f:2.3~2.53	0.75	2.7	5.3	6.0	7.5	9.0	10.7	13.6	16.0
		Max: 300"	H: +/- 15%		0.95	3.4	6.7	7.6	9.5	11.4	13.4	17.0	20.1

AH-A22020	A01	Min: 50"	V: +/- 50%	f:2.3~2.57	0.95	3.4	6.7	7.6	9.5	11.4	13.4	17.0	20.1
		Max: 300"	H: +/- 15%		1.22	4.3	8.6	9.7	12.2	14.6	17.2	21.9	25.8

AH-A21010	A03	Min: 50"	V: +/- 50%	f:2.3~3.3	1.52	5.4	10.8	12.2	15.2	18.3	21.5	27.4	32.2
		Max: 300"	H: +/- 15%		2.92	10.3	20.7	23.4	29.2	35.1	41.4	52.6	62.0

AH-A23010	A13	Min: 50"	V: +/- 50%	f:2.3~2.4	2.90	10.3	20.6	23.2	29.0	34.8	41.1	52.3	61.5
		Max: 300"	H: +/- 15%		5.50	19.5	38.9	44.0	55.0	66.0	77.8	99.0	116.6

AH-A22040**	A05	Min: 50"	V: +/- 50%	f:2.0~2.3	1.22	4.3	8.6	9.7	12.2	14.6	17.2	21.9	25.8
		Max: 300"	H: +/- 15%		1.53	5.4	10.8	12.2	15.3	18.4	21.6	27.5	32.4

0001-5045	500	Min: ∞	V: +/- 50%	f:2.8	4.85	17.2	34.3	38.8	48.5	58.2	68.6	87.2	102.8
		Max: ∞	H: +/- 15%		8.66	30.7	61.3	69.3	86.6	103.9	122.6	155.9	144

0001-5046	087	Min: ∞	V: +/- 50%	f:3.5	9.15	32.4	64.8	73.2	91.5	109.8	129.4	164.7	193.9
		Max: ∞	H: +/- 15%		15.24	53.9	107.9	121.9	152.4	182.9	215.6	274.3	144

* Standard lens (47 line pair/mm)

** Superior Image Quality (67 line pair/mm)

*** Please call Eiki Support before ordering this lens Tel. 800/242-3454 option 4

How to use the T/W column. If your screen size does not appear on this chart, use the T/W column to find the lens you need.

Divide the Throw distance by the screen Width to get your "target T/W number". Then, look for a lens with a T/W range that covers it.

These tables are a simulation. They are the result of averaging and rounding. Lens performance is actually not linear, and non-mathematical: variations in behavior do occur.

Calculations are from the front glass of the lens and accurate to approximately +/- 3%. Specifications are subject to change without notice.

Eiki International, Inc. Tel: 800-242-3454, Fax: 800-457-3454, E-mail: usa@eiki.com

In Canada: Tel: 800-563-3454, E-mail: canada@eiki.com

Website: <http://www.eiki.com>